


Item details

Description	<b>TUB</b>												
Main application areas	<b>Catering, Party and Fast-Food</b>												
Product line	<b>Faerch</b>												
<p>Decoration technology</p> <table border="0"> <tr> <td><input type="checkbox"/> Serigraphy</td> <td><input type="checkbox"/> Rotogravure</td> <td><input type="checkbox"/> Offset</td> <td><input type="checkbox"/> Flexo</td> </tr> <tr> <td><input type="checkbox"/> Trans-Deco</td> <td><input type="checkbox"/> I.M.L.</td> <td><input type="checkbox"/> Adhesive label</td> <td><input type="checkbox"/> Shrink sleeve</td> </tr> <tr> <td colspan="4"><input type="checkbox"/> Paperboard Sleeve</td> </tr> </table>		<input type="checkbox"/> Serigraphy	<input type="checkbox"/> Rotogravure	<input type="checkbox"/> Offset	<input type="checkbox"/> Flexo	<input type="checkbox"/> Trans-Deco	<input type="checkbox"/> I.M.L.	<input type="checkbox"/> Adhesive label	<input type="checkbox"/> Shrink sleeve	<input type="checkbox"/> Paperboard Sleeve			
<input type="checkbox"/> Serigraphy	<input type="checkbox"/> Rotogravure	<input type="checkbox"/> Offset	<input type="checkbox"/> Flexo										
<input type="checkbox"/> Trans-Deco	<input type="checkbox"/> I.M.L.	<input type="checkbox"/> Adhesive label	<input type="checkbox"/> Shrink sleeve										
<input type="checkbox"/> Paperboard Sleeve													
<p>Production technology</p> <table border="0"> <tr> <td><input type="checkbox"/> Injection</td> <td><input type="checkbox"/> Piberplast</td> </tr> <tr> <td><input checked="" type="checkbox"/> Thermoforming</td> <td><input type="checkbox"/> Stampplast</td> </tr> <tr> <td><input type="checkbox"/> Others</td> <td><input type="checkbox"/> ESBE Italiana</td> </tr> <tr> <td></td> <td><input checked="" type="checkbox"/> Others</td> </tr> </table>		<input type="checkbox"/> Injection	<input type="checkbox"/> Piberplast	<input checked="" type="checkbox"/> Thermoforming	<input type="checkbox"/> Stampplast	<input type="checkbox"/> Others	<input type="checkbox"/> ESBE Italiana		<input checked="" type="checkbox"/> Others				
<input type="checkbox"/> Injection	<input type="checkbox"/> Piberplast												
<input checked="" type="checkbox"/> Thermoforming	<input type="checkbox"/> Stampplast												
<input type="checkbox"/> Others	<input type="checkbox"/> ESBE Italiana												
	<input checked="" type="checkbox"/> Others												
To be closed with	Related items												
<b>P5187</b>													




Technical data sheet

Raw Material	<b>C-PET</b>	Also transparent <input type="checkbox"/>									
Weight gr.	<b>26,8</b>										
<p>Dimensions and volume</p> <table border="0"> <tr> <td>Height</td> <td>Brimful volume</td> <td>Useful volume</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> <tr> <td><b>27</b></td> <td><b>480</b></td> <td></td> </tr> </table>			Height	Brimful volume	Useful volume				<b>27</b>	<b>480</b>	
Height	Brimful volume	Useful volume									
<b>27</b>	<b>480</b>										
<p>External dimensions mm</p> <table border="0"> <tr> <td>Length</td> <td>Width</td> <td>Diameter</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> <tr> <td><b>187</b></td> <td><b>137</b></td> <td></td> </tr> </table>			Length	Width	Diameter				<b>187</b>	<b>137</b>	
Length	Width	Diameter									
<b>187</b>	<b>137</b>										
<p>Internal dimensions mm</p> <table border="0"> <tr> <td>Length</td> <td>Width</td> <td>Diameter</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> <tr> <td><b>171</b></td> <td><b>121</b></td> <td></td> </tr> </table>			Length	Width	Diameter				<b>171</b>	<b>121</b>	
Length	Width	Diameter									
<b>171</b>	<b>121</b>										
<p>Base dimensions mm</p> <table border="0"> <tr> <td>Length</td> <td>Width</td> <td>Diameter</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> <tr> <td><b>157</b></td> <td><b>107</b></td> <td></td> </tr> </table>			Length	Width	Diameter				<b>157</b>	<b>107</b>	
Length	Width	Diameter									
<b>157</b>	<b>107</b>										
<p>Key list of raw materials</p> <table border="0"> <tr> <td><b>A-PET</b> Polyethylene terephthalate amorphous</td> <td><b>C-PET</b> Polyethylene terephthalate crystallized</td> </tr> <tr> <td><b>LDPE</b> Low Density Polyethylene (or Polythene)</td> <td><b>HDPE</b> High Density Polyethylene (or Polythene)</td> </tr> <tr> <td><b>PS</b> Polystyrene</td> <td><b>PP</b> Polypropylene</td> </tr> <tr> <td><b>PVC</b> Polyvinyl chloride</td> <td><b>SBS</b> Poly(styrene-Butadiene-styrene)</td> </tr> </table>			<b>A-PET</b> Polyethylene terephthalate amorphous	<b>C-PET</b> Polyethylene terephthalate crystallized	<b>LDPE</b> Low Density Polyethylene (or Polythene)	<b>HDPE</b> High Density Polyethylene (or Polythene)	<b>PS</b> Polystyrene	<b>PP</b> Polypropylene	<b>PVC</b> Polyvinyl chloride	<b>SBS</b> Poly(styrene-Butadiene-styrene)	
<b>A-PET</b> Polyethylene terephthalate amorphous	<b>C-PET</b> Polyethylene terephthalate crystallized										
<b>LDPE</b> Low Density Polyethylene (or Polythene)	<b>HDPE</b> High Density Polyethylene (or Polythene)										
<b>PS</b> Polystyrene	<b>PP</b> Polypropylene										
<b>PVC</b> Polyvinyl chloride	<b>SBS</b> Poly(styrene-Butadiene-styrene)										



Packing details



Box		
Packing details	2 STACKS OF 117 PIECES LYING ON THE LONG SIDE OF THE BOX AND ARRANGED ON 2 LAYERS	
Packing	<b>FE04</b>	
Length (L) (mm)	<b>390</b>	
Width (B) (mm)	<b>390</b>	
Height (H) (mm)	<b>280</b>	
Volume (mc.)	<b>0,04258800</b>	
Gross Weight kg.*	<b>13,54</b>	
Pieces / box	<b>468</b>	

Pallet

Pallet	<b>FE04P</b>	<b>80 X 120</b>
Height cm. **	<b>183</b>	
Weight kg.***	<b>502,53</b>	
Boxes / layer	<b>6</b>	
No. of layers	<b>6</b>	
Boxes / pallet	<b>36</b>	
Volume (mc.) ****	<b>1,7568</b>	
Pieces / pallet	<b>16848</b>	
Pallet notes		

Notes

- \* The gross weight of the box is inclusive of all the additional elements (packing weight, tape, liner, etc.)
- \*\* The total height is inclusive of the pallet height
- \*\*\* The gross weight of the pallet includes the weight of all the additional elements (weight of every single box, stretch film, weight of the pallet, etc.)
- \*\*\*\* The total volume includes also the pallet volume

